



SaniSure™
Be sure.

PRESS RELEASE

SaniSure, Inc. is pleased to introduce SaniSure™ Cap2v8
for use with your GL45 & 38-430 bottles.



The SaniSure Cap2v8 tube and cap system is a unique integrated cap and tube system providing for aseptic transfer, storage, and sampling.

The one-piece molded cap reduces contamination & product loss that traditionally is associated with barbed fittings. This innovative design “closes” your system protecting product integrity and providing an aseptic seal for high purity biologicals.

The flexibility of this product line allows customers the ability to custom configure systems with unique tubing sizes, lengths, and other accessories. The Cap2v8 tubing for the GL45 and 38-430 bottles is made from C-Flex® and the caps made of polypropylene. While the Cap2v8 standard cap and tube system has been designed and optimized to fit the GL45 and 38-430 bottles from various manufacturers, other custom container systems can be provided.

The SaniSure Cap2v8 system is designed for single-use, meets USP Class VI, lot-traceable, packaged in a certified ISO Class 7 Clean Room, and provides quick turn around lead times on small or large volume lots. With the option to have these assemblies shipped pre-irradiated or not pre-irradiated; provide customers the flexibility of implementing technology specific to their individual needs.

From research to process, whether bench top scale, pilot plant, or manufacturing this system offers a cap system, a tube and cap system stand alone product or a tube and cap system component part of an overall assembly.

Please contact us to see how the SaniSure Cap2v8 product line can benefit your business. If you would like to see samples for proof of concept or to order any of the SaniSure Cap2v8 products, contact SaniSure, Inc at 1-877-777-3005; PO BOX 2360, Moorpark, CA 93021

About SaniSure, Inc.

SaniSure, Inc. is a provider of single-use systems as well as a cGMP component manufacturer focusing on engineered solutions for the Biopharmaceutical and Biotech industries - FROM CONCEPT TO PROTOTYPE TO PRODUCTION. These single use systems are assembled in an ISO Class 7 (10,000) clean room. SaniSure, Inc.'s focus is to provide help in design, development, and optimization of current processes. We can assist you with customized assemblies to help improve safety, reduce labor costs, improve production efficiency, and reduce overall production costs, thereby improving ease of implementation and speed to market. For more information on SaniSure, Inc. and our growing line of single use products, please visit www.SaniSure.com. Contact: Jeff Chase, Sales & Marketing Manager, 317-859-9878, jchase@sansisure.com

www.SaniSure.com

SaniSure Inc.
P.O. Box 2360
Moorpark, CA 93021
Toll Free (877) 777-3005